
610 S. Maumee Street, Tecumseh, MI 49286

www.ididit.com

Ph: 517-424-0577

CUSTOM UNIVERSAL TILT COLUMN SHIFT (Standard measurements are shown)



To customize your column please download this form & fill in the fields below. Mark the customer drawing if necessary, add any additional comments and sign. Once you are satisfied, save the filled out form and email it to us at sales@ididit.com.

| Reposition Wire Harness:″ from Top of Column |
|---|
| Overall wire harness position is measured from top of head to top of wire harness |
| location. Standard is 13 $1/4''$. Max total is 22''. |
| Rotation of Wire Harness: : o'clock (per half hour) |
| Rotation starts at 12 o'clock from seating position |
| Add/Move Neutral Safety Switch:" (up to 2" from bottom of sleeve) |
| NeutralSafety Switch is measured from top of sleeve to middle of switch. Switch must be |
| located below wire harness. |
| Rotation of Neutral Safety Switch:: o'clock |
| Rotation starts at 12 o'clock from seating position |
| Change Cup Length:" Minimum of 15/16", Standard is 27/8" |
| Shortened cup lenths may expose internal column wiring. |
| Tube Diameter (check one): 2" 2 1/4"(Standard) |
| Shaft Length: " Out of tube (Max 8") |
| Shaft Type (check one): 1" 48 3/4"DD 1" DD 3/4" 36 |
| Columns under 22" can ONLY be built using 3/4" DD output shaft |
| Overall Length: (from top of head to the bottom of shaft)″ |
| Ignition: Yes No |
| Column Finish (check one): Paintable Steel Chrome Black |
| Column Finish (check one): Fainlable Sleer Chrome Diack |
| |
| Brushed Aluminum Polished Aluminum |
| Brushed Aluminum Polished Aluminum Vehicle: Year: |
| Vehicle: Year: |
| |
| Vehicle: Year: |
| Vehicle: Year: AdditionalComments: |
| Vehicle: Year: |
| Vehicle: Year: AdditionalComments: |
| Vehicle: AdditionalComments: |

UniversalTiltColumnShift_CustomForm_Rev2_032023

Date: ____/___/____