DIT UNIVERSAL TILT FLOOR SHIFT COLUMN (Standard measurements are shown)

610 S. Maumee Street, Tecumseh, MI 49286 Ph: 517-424-0577 www.ididit.com

> To customize your column please download this form & fill in the fields below. Mark the customer drawing if necessary, add any additional comments and sign. Once you are satisfied, save the filled out form and email it to us at sales@ididit.com.

4″ Sleeve	sales@ididif.com.
(Length Cannol be Changed)	Reposition Wire Harness:″ from Top of Column
1/4"	Overall wire harness position is measured from top of head to top of wire harness location. Standard is 11-1/2". Max total is 22". Rotation of Wire Harness: : o'clock (per half hour)
	Rotation starts at 12 o'clock from seating position
3 5/16" Cup Wire Harness	Change Cup Length:" Minimum of 1 1/2", Standard is 3 5/16" Shortened cup lengths may exposed internal column wiring
	Tube Diameter (check one): 2" (Standard) 2 1/4"
	Shaft Length:″ Out of tube (Max 8″)
	Shaft Type (check one): 1" 48 3/4"DD 1" DD 3/4" 36
	Columns under 22" can ONLY be built using 3/4" DD output shaft
	Overall Length: (from top of head to the bottom of shaft)"
	Ignition: Yes No (Ignition not available on aluminum columns)
	Column Finish (check one): Paintable Steel Chrome Black
	Brushed Aluminum Polished Aluminum
	Vehicle:Year:
	AdditionalComments:
Tube	
← 2″ →	
	Name:
	Phone: Email:
	By typing my name below I agree to recognize this as my legal signature for this document. The information I have supplied is correct and I assume responsibility for the requests that have been made on this form.
	Signature:
Shaft Type	Date:// UniversalTiltFloorShift_CustomForm_Rev 3 _032023